

BERGALAV



FOOD & BEVERAGE

Food industry
Cleaning



APPLICATIONS

For hot water cleaning in food processing plants with possible occasional use with steam up to 160°C.

ADVANTAGES

- Highly flexible.
- Specially adapted to keep round on reels.
- Contains no phthalate.

TECHNICAL DESCRIPTION

Inner tube: food grade quality EPDM, white, smooth.

Reinforcement: synthetic textile.

Cover: weather resistant EPDM, blue, smooth.

Temperature range: -30°C to +160°C.

STANDARD/APPROVAL

EU regulations No. 1935/2004, 2023/2006.



FDA regulation No. 21 CFR 177.2600.



French legislation.




All relevant migrations tests (France and FDA) were performed by the French institute of Poitiers (IANESCO) and confirmed compliant.

COUPLINGS/FITTINGS

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

COMPLEMENTARY INFORMATION

Please refer to our cleaning guidelines, available upon request and from our website.



**FOOD & BEVERAGE****BERGALAV**

ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
10.0 ±0.6	18.0 ±0.7	10	30	75	0.25	20	5501308	
10.0 ±0.6	18.0 ±0.7	10	30	75	0.25	40	5501309	
13.0 ±0.6	22.0 ±0.7	10	30	95	0.35	20	5500857	
13.0 ±0.6	22.0 ±0.7	10	30	95	0.35	40	5500858	
16.0 ±0.7	25.0 ±0.8	10	30	110	0.41	20	5500859	
16.0 ±0.7	25.0 ±0.8	10	30	110	0.41	40	5500860	
19.0 ±0.8	29.0 ±0.9	10	30	135	0.54	20	5500861	
19.0 ±0.8	29.0 ±0.9	10	30	135	0.54	40	5500862	
25.0 ±1.0	36.0 ±1.0	10	30	180	0.74	20	5500863	
25.0 ±1.0	36.0 ±1.0	10	30	180	0.74	40	5500864	

Tolerance on length: ±1% (ISO 1307 Standard).

**TRELLEBORG**