

# STARKLER



## GENERAL INDUSTRY

Hot water and multipurpose chemicals



### APPLICATIONS

A versatile hose for high pressure cleaning operations and general discharge service using hot or cold water and many other fluids (see chemical resistance table for EPDM).

Suitable for all sectors: building and public works, industry, agriculture, etc.

### ADVANTAGES

- ┆ Extremely resistant to ageing and atmospheric conditions.
- ┆ Wide range of operating temperatures (-30 °C to +100 °C).
- ┆ Wide range of diameters.
- ┆ Excellent mechanical properties.
- ┆ Resistant to many fluids.
- ┆ Attractive, well-finished appearance.
- ┆ Long service life.

### TECHNICAL DESCRIPTION

Inner tube: EPDM, black, smooth.

Reinforcement: synthetic textile.

Cover: EPDM, black, smooth for ID from 12.7 to 25.4mm, fabric impression for ID from 30 to 38mm.

Temperature range: -30 °C to +100 °C.

### STANDARD/APPROVAL

In compliance with ISO 1403 type 2 (except branding).



12.7-25.4mm



and in opposite:



30-38mm





## GENERAL INDUSTRY

## STARKLER



ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
12.7 ±0.6	4	20.7 ±0.7	20	60	55	0.27	20	0060012	1
12.7 ±0.6	4	20.7 ±0.7	20	60	55	0.27	40	0060013	1
12.7 ±0.6	4	20.7 ±0.7	20	60	55	0.27	80	0060990	1
15.8 ±0.7	4.1	24.0 ±0.8	20	60	70	0.33	20	0060014	1
15.8 ±0.7	4.1	24.0 ±0.8	20	60	70	0.33	40	0060015	1
15.8 ±0.7	4.1	24.0 ±0.8	20	60	70	0.33	80	0060991	1
19.4 ±0.7	4.5	28.4 ±0.8	20	60	85	0.43	20	0060016	1
19.4 ±0.7	4.5	28.4 ±0.8	20	60	85	0.43	40	0060017	1
19.4 ±0.7	4.5	28.4 ±0.8	20	60	85	0.43	80	0060992	1
25.4 ±1.0	4.8	35.0 ±1.1	20	60	100	0.58	20	0060018	1
25.4 ±1.0	4.8	35.0 ±1.1	20	60	100	0.58	40	0060019	1
25.4 ±1.0	4.8	35.0 ±1.1	20	60	100	0.58	80	0060993	1
30.0 ±1.0	4.25	39.0 ±1.0	10	30	240	0.72	20	0200259	1
30.0 ±1.0	4.25	39.0 ±1.0	10	30	240	0.72	40	0200260	1
32.0 ±1.0	4.25	41.0 ±1.0	10	30	260	0.77	20	0123234	1
32.0 ±1.0	4.25	41.0 ±1.0	10	30	260	0.77	40	0123239	1
35.0 ±1.0	4.25	44.0 ±1.0	10	30	280	0.83	20	0200261	1
35.0 ±1.0	4.25	44.0 ±1.0	10	30	280	0.83	40	0200262	1
38.0 ±1.0	4.25	47.0 ±1.0	10	30	310	0.89	20	0123245	200
38.0 ±1.0	4.25	47.0 ±1.0	10	30	310	0.89	40	0070387	200

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version



TRELLEBORG