

COLORADO S



GENERAL INDUSTRY

Water
Discharge applications



APPLICATIONS

Water discharge for all types of industrial and agricultural medium pressure applications in harsh environments.

ADVANTAGES

- † Extremely resistant to ageing and atmospheric conditions.
- † Coils flat for easy storage and handling.
- † A robust construction to resist impact, kinking and abrasion.
- † For fluids up to 100 °C.
- † Wide range of diameters.

TECHNICAL DESCRIPTION

Inner tube: EPDM, white, smooth.


Reinforcement: synthetic textile.

Cover: EPDM, orange, fabric impression.

Temperature range: -30 °C to +100 °C.

STANDARD/APPROVAL

In compliance with ISO 1403 type 1 (except branding).



**GENERAL INDUSTRY****COLORADO S**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
40.0	4.25 ±0.75	49.0 ±1.0	10	28	320	0.91	20	0062298	1
40.0	4.25 ±0.75	49.0 ±1.0	10	28	320	0.91	40	0062297	1
45.0	4.25 ±0.75	54.0 ±1.0	10	28	360	1.01	20	0062303	1
45.0	4.25 ±0.75	54.0 ±1.0	10	28	360	1.01	40	0062302	1
50.0	4.25 ±0.75	60.0 ±1.0	10	28	500	1.26	20	0062308	1
50.0	4.25 ±0.75	60.0 ±1.0	10	28	500	1.26	40	0062307	1
60.0	4.25 ±0.75	70.0 ±1.5	10	28	600	1.51	20	0062318	1
60.0	4.25 ±0.75	70.0 ±1.5	10	28	600	1.51	40	0062317	1
65.0	4.25 ±0.75	76.5 ±1.5	10	28	650	1.8	20	0200059	120
65.0	4.25 ±0.75	76.5 ±1.5	10	28	650	1.8	40	0200060	1
70.0	5.75 ±1.00	81.5 ±1.5	10	28	700	2.01	20	0062328	1
75.0	5.75 ±1.00	86.5 ±1.5	10	28	750	2.15	20	0200061	120
75.0	5.75 ±1.00	86.5 ±1.5	10	28	750	2.15	40	0200062	1
80.0	5.75 ±1.00	92.0 ±1.5	10	28	850	2.43	20	0062336	1
80.0	5.75 ±1.00	92.0 ±1.5	10	28	850	2.43	40	0062337	1
89.0	5.75 ±1.00	101.0 ±1.5	10	28	900	2.71	20	0062339	1
89.0	5.75 ±1.00	101.0 ±1.5	10	28	900	2.71	40	0062349	1
100.0	5.75 ±1.00	112.0 ±1.5	10	28	1000	3	20	0062341	1
120.0	5.75 ±1.00	131.5 ±2.0	5	13	1200	3.41	10	0200006	20

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version

**TRELLEBORG**