

VENDANGE



FOOD & BEVERAGE

Food industry
Transfer



APPLICATIONS

Specially designed for transfer of fresh grapes in wine processing industries.

AVANTAGES

- ┆ Outstanding flexibility and easy handling.
- ┆ Weak tractive effort thanks to slicking cover.
- ┆ Smooth, seamless, white tube, that does not propagate bacterial growth.
- ┆ Resistant to cleaning with most common detergents (see our cleaning guideline for details) or with steam at max. 110 °C during 10 minutes max.
- ┆ Non-marking cover.
- ┆ Contains no phthalate.

TECHNICAL DESCRIPTION

Inner tube food grade quality NR, color, smooth.

Reinforcement synthetic textile with embedded steel helix.

Cover special polymer-based, color.

Temperature range -30 °C to +80 °C.

STANDARD/APPROVAL

EU regulations No. 1935/2004, 2023/2006.



FDA regulation No. 21 CFR 177.2600.



French legislation.



All relevant migrations tests (France and FDA) were performed by the French institute of Poitiers (IANESCO) and confirmed compliant.

COUPLINGS/FITTINGS

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

COMPLEMENTARY INFORMATION

Please refer to our cleaning guidelines, available upon request and from our website.



**FOOD & BEVERAGE****VENDANGE**

ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
100.0 -0/+1	117.0 ±1.5	6	18	140	3.32	20	5026072	
125.0 -0/+2	142.5 ±2.0	6	18	170	4.1	10	5501457	
125.0 -0/+2	142.5 ±2.0	6	18	170	4.1	20	5501458	
150.0 -0/+2	167.5 ±2.0	6	18	200	4.97	10	5501459	
150.0 -0/+2	167.5 ±2.0	6	18	200	4.97	20	5501460	

Tolerance.

Digital version

