

ALTIPLUS



AGRICULTURE

Farm
Spraying



APPLICATIONS

High pressure agricultural spraying (fungicide, weed killers, insecticides, etc.).

Also suitable for paint spraying and disinfection of buildings or high pressure water discharge.

ADVANTAGES

- | A high performance hose for extra heavy duty service.
- | Excellent coupling retention.
- | A wide range of diameters.
- | Non-marking cover.
- | Good ageing and weather resistance.

TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.

Reinforcement: synthetic textile.

Cover: SBR, beige, with two groups of three ribs.

Temperature range: -30°C to +70°C.


STANDARD/APPROVAL

EN ISO 1401, type C for ID<16mm, type B for ID≥16mm.

ISO

COMPLEMENTARY INFORMATION

50% of the volume in each delivery will be random lengths, shortest length of 10m, at least 50% will be in fixed length mentioned in the table.





ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
8.0 ±0.5	16.0 ±0.6	60	240	40	0.24	40	5501371	∅
8.0 ±0.5	16.0 ±0.6	60	240	40	0.24	160	5501372	∅
9.0 ±0.5	17.5 ±0.6	60	240	40	0.28	40	5501373	1360
10.0 ±0.5	18.5 ±0.6	60	240	45	0.29	40	5501375	∅
10.0 ±0.5	18.5 ±0.6	60	240	45	0.29	50	5012558	∅
10.0 ±0.5	18.5 ±0.6	60	240	45	0.29	60	5012557	∅
10.0 ±0.5	18.5 ±0.6	60	240	45	0.29	100	5012556	∅
10.0 ±0.5	18.5 ±0.6	60	240	45	0.29	160	5501376	∅
10.0 ±0.5	18.5 ±0.6	60	240	45	0.29	200	5501377	∅
12.5 ±0.6	21.0 ±0.7	60	240	50	0.31	40	5501378	∅
12.5 ±0.6	21.0 ±0.7	60	240	50	0.31	80	5501379	∅
12.5 ±0.6	21.0 ±0.7	60	240	50	0.31	160	5501380	∅
16.0 ±0.7	26.5 ±0.8	40	160	80	0.53	40	5501381	∅
16.0 ±0.7	26.5 ±0.8	40	160	80	0.53	120	5501382	840

Tolerance on length: ±1% (ISO 1307 Standard).

∅ Upon availability.

Digital version

