

KLERIX



CONSTRUCTION & INFRASTRUCTURE

Drain and sewer cleaning



APPLICATIONS

For use in sewer cleaning water pressure applications.
Suitable for replacing hydraulic hoses used in this application.

ADVANTAGES

- ▮ Abrasion and weather resistant cover compound.
- ▮ Smooth cover, low friction.
- ▮ Long lengths.

TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.

Reinforcement: steel, braided.

Cover: SBR/NR, black, smooth.

Temperature range: -30°C to +80°C.


COUPLINGS/FITTINGS

Hydraulic coupling.

COMPLEMENTARY INFORMATION

Delivered without couplings.

Embossed branding





ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
13.0 ±0.8	5	23.0 ±0.8	200	500	70	0.45	40	0071107	☒
13.0 ±0.8	5	23.0 ±0.8	200	500	70	0.45	60	0071108	☒
13.0 ±0.8	5	23.0 ±0.8	200	500	70	0.45	80	0071109	☒
13.0 ±0.8	5	23.0 ±0.8	200	500	70	0.45	100	0071110	☒
19.0 ±0.8	6.25	31.5 ±0.8	200	500	95	0.82	40	5010435	☒
19.0 ±0.8	6.25	31.5 ±0.8	200	500	95	0.82	60	0071113	☒
19.0 ±0.8	6.25	31.5 ±0.8	200	500	95	0.82	120	0071116	☒
25.0 ±1.0	6.55	38.1 ±1.0	200	500	110	1.14	60	0071117	☒
25.0 ±1.0	6.55	38.1 ±1.0	200	500	110	1.14	80	0071118	☒
25.0 ±1.0	6.55	38.1 ±1.0	200	500	110	1.14	100	0071119	☒
25.0 ±1.0	6.55	38.1 ±1.0	200	500	110	1.14	120	0071120	☒
32.0 ±1.2	6.95	45.9 ±1.2	200	500	150	1.57	60	0071121	☒
32.0 ±1.2	6.95	45.9 ±1.2	200	500	150	1.57	80	0071122	☒
32.0 ±1.2	6.95	45.9 ±1.2	200	500	150	1.57	100	0071123	☒
32.0 ±1.2	6.95	45.9 ±1.2	200	500	150	1.57	120	0071124	☒

Tolerance on length: ±1% (ISO 1307 Standard).

☒ Upon availability.

Digital version



TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING