

ASPIKLER N



**CONSTRUCTION &
INFRASTRUCTURE**



Drain and sewer cleaning

APPLICATIONS

For sewer suction.

Also for suction or delivery of abrasive materials on stationary systems and for cassette applications on sewer cleaning vehicles.

AVANTAGES

- High resistance to abrasive environment and abrasive transportation media.
- Suitable both for suction and pressure.

TECHNICAL DESCRIPTION

Inner tube SBR, color, smooth.

Reinforcement synthetic textile cords with embedded steel helix.

Cover SBR/NR, color, fabric impression.

Temperature range -30°C to +80°C.



**CONSTRUCTION &
INFRASTRUCTURE****ASPIKLER N**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
100.0 ±1.0	8	116.5 ±1.5	6	15	0.9	450	4.3	20	0095016	1
100.0 ±1.0	8	116.5 ±1.5	6	15	0.9	450	4.3	40	0096724	1
102.0 ±1.0	8	118.0 ±1.5	6	15	0.9	450	4.38	20	5513565	1
125.0 ±1.2	9.5	144.0 ±1.5	6	15	0.9	550	6.3	20	0094152	1
125.0 ±1.2	9.5	144.0 ±1.5	6	15	0.9	550	6.3	40	5009671	1
127.0 ±1.2	9.5	146.0 ±1.5	6	15	0.9	550	6.39	20	5513566	1
150.0 ±1.2	10	170.0 ±1.5	6	15	0.9	650	7.77	20	5008847	1
152.0 ±1.2	10	172.0 ±1.5	6	15	0.9	650	7.87	20	5513567	1

Tolerance.

Digital version

WWW.TRELLEBORG.COM/FLUIDHANDLING