

# ASSAINIX



## CONSTRUCTION & INFRASTRUCTURE

Drain and sewer cleaning



### APPLICATIONS

Pumping installations, suction and delivery.

Sewer and tank truck applications.

### ADVANTAGES

- † Excellent kink resistance even at small bending radius.
- † Withstands 0.8bar vacuum.
- † Smooth cover to prevent friction on sharp edges of manholes, walls fences, etc.
- † This hose can be produced with straight or enlarged ends (from 3 to 12mm) to fit all types of couplings.
- † High resistance to abrasive environment.

### TECHNICAL DESCRIPTION

Inner tube: NR, black, smooth.


Reinforcement: synthetic textile cords with embedded steel helix.

Cover: NR, black, fabric impression.

Temperature range: -30°C to +60°C.

### COMPLEMENTARY INFORMATION

Other lengths and other diameters like diam.120mm could be produced on request.



**CONSTRUCTION &  
INFRASTRUCTURE****ASSAINIX**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
100.0	10 ±2.5	120.0 ±2.0	4	12	0.8	800	5.21	4.5	0060278	1
120.0	10 ±2.5	140.0 ±2.0	4	12	0.8	960	7.29	4.5	0095036	9
120.0	10 ±2.5	140.0 ±2.0	4	12	0.8	960	7.3	6	5006886	12

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version



[WWW.TRELLEBORG.COM/FLUIDHANDLING](http://WWW.TRELLEBORG.COM/FLUIDHANDLING)