

# SABLEX



## CONSTRUCTION & INFRASTRUCTURE

Blasting and guniting



### APPLICATIONS

For cleaning and shot blasting castings, metal, stone and concrete surfaces.

### ADVANTAGES

- † Small tolerances, therefore easy to couple.
- † Longitudinally stable i.e. the length will not alter under pressure (unstable hoses result in the operator losing control when pressure is applied).
- † Light weight and flexible for easy handling.
- † Conductive inner tube compound gives increased safety for the operator, since there is no risk of wire breakage in use.

### TECHNICAL DESCRIPTION

Inner tube: wear resistant NR, black, smooth.


Reinforcement: synthetic textile.

Cover: wear and weather resistant SBR, black, fabric impression.

Temperature range: -30 °C to +70 °C.

Electrical properties: conductive tube,  $R < 2 \cdot 10^6 \Omega/m$ .

Special properties: abrasion resistance of tube  $< 40mm^3$  according to ISO 4649.





ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
13.0	7 ±0.50	27.0 ±1.0	12	40	65	0.58	40	0060061	1
16.0	7 ±0.50	30.0 ±1.0	12	40	80	0.68	20	0028719	400
16.0	7 ±0.50	30.0 ±1.0	12	40	80	0.68	40	0028720	400
19.0	7.5 ±0.50	34.0 ±1.0	12	40	100	0.78	20	0028745	1
19.0	7.5 ±0.50	34.0 ±1.0	12	40	100	0.78	40	0028746	1
25.0	7 ±0.50	39.0 ±1.0	12	40	125	0.86	20	0060969	1
25.0	7 ±0.50	39.0 ±1.0	12	40	125	0.86	40	0060970	1
32.0	8 ±0.50	48.0 ±1.0	12	40	160	1.3	20	0060971	1
32.0	8 ±0.50	48.0 ±1.0	12	40	160	1.3	40	0060972	1
32.0	11 ±0.50	54.0 ±1.0	12	40	140	1.85	20	0070785	200
32.0	11 ±0.50	54.0 ±1.0	12	40	140	1.85	40	0070786	200
35.0	9 ±0.50	53.0 ±1.0	12	40	190	1.57	40	0070788	200
38.0	10 ±0.50	58.0 ±1.0	12	40	170	1.89	20	0070789	200
38.0	10 ±0.50	58.0 ±1.0	12	40	170	1.89	40	0070790	1
40.0	10 ±0.50	60.0 ±1.0	12	40	180	1.97	20	0028786	600
40.0	10 ±0.50	60.0 ±1.0	12	40	180	1.97	40	0028787	1
42.0	9 ±0.50	60.0 ±1.0	12	40	240	1.81	20	0070791	200
42.0	9 ±0.50	60.0 ±1.0	12	40	240	1.81	40	0070792	200
50.0	10 ±0.75	70.0 ±1.5	12	40	250	2.36	40	0060974	1
63.0	10 ±0.75	83.0 ±1.5	12	40	325	2.9	40	0060077	160
65.0	10 ±0.75	85.0 ±1.5	12	40	320	2.95	20	0070797	160
65.0	10 ±0.75	85.0 ±1.5	12	40	320	2.95	40	0070798	160
76.0	10 ±0.75	96.0 ±1.5	12	40	400	3.42	40	0070784	120
102.0	10 ±0.75	122.0 ±1.5	12	40	550	4.4	40	0028860	80

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version



**TRELLEBORG**