

CASCADE



GENERAL INDUSTRY

Air and water



APPLICATIONS

Water discharge under pressure on industrial or urban sites and all water discharge applications in building and public works.

ADVANTAGES

- Extremely resistant to ageing and atmospheric conditions.
- Highly flexible and easy-to-hold due to the fluted cover.

TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.


Reinforcement: synthetic textile.

Cover: EPDM, green, fluted.

Temperature range: -30°C to +70°C.

STANDARD/APPROVAL

In compliance with ISO 1403 type 2 (except branding).



**GENERAL INDUSTRY****CASCADE**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
12.7 ±0.6	4	20.7 ±0.7	10	30	70	0.28	20	0061511	☒
12.7 ±0.6	4	20.7 ±0.7	10	30	70	0.28	40	0061510	∣
15.8 ±0.7	4.1	24.0 ±0.8	10	30	80	0.34	20	0061521	∣
15.8 ±0.7	4.1	24.0 ±0.8	10	30	80	0.34	40	0061520	∣
15.8 ±0.7	4.1	24.0 ±0.8	10	30	80	0.34	80	0061522	1760
19.4 ±0.7	4.5	28.4 ±0.8	10	30	120	0.45	20	0061541	∣
19.4 ±0.7	4.5	28.4 ±0.8	10	30	120	0.45	40	0061540	∣
19.4 ±0.7	4.5	28.4 ±0.8	10	30	120	0.45	80	0061542	∣
25.4 ±1.0	4.8	35.0 ±1.1	10	30	150	0.6	20	0061551	∣
25.4 ±1.0	4.8	35.0 ±1.1	10	30	150	0.6	40	0061550	∣

Tolerance on length: ±1% (ISO 1307 Standard).

☒ Upon availability.

Digital version

**TRELLEBORG**