

# AP RED



## GENERAL INDUSTRY

Water  
Discharge applications



### APPLICATIONS

Water discharge for heavy duty applications.

### ADVANTAGES

- ┆ Coils flat for easy storage and handling.
- ┆ Light weight.
- ┆ Long length.
- ┆ High bursting pressure.
- ┆ Wide range of diameters.

### TECHNICAL DESCRIPTION

Inner tube: PVC, black, smooth.

Reinforcement: synthetic textile.

Cover: PVC, red, smooth.

Temperature range: -10°C to +40°C.

### COMPLEMENTARY INFORMATION

Working pressure and bursting pressure mentioned are valid at +20°C.





GENERAL INDUSTRY

AP RED



| ID<br>mm | WORKING<br>PRESSURE<br>bar | BURSTING<br>PRESSURE<br>bar | WEIGHT<br>kg/m | LENGTH<br>m | ARTICLE NUMBER | STOCK ( ) or min.<br>order<br>m |
|----------|----------------------------|-----------------------------|----------------|-------------|----------------|---------------------------------|
| 40.0     | 14                         | 42                          | 0.44           | 50          | 0201470        | 1                               |
| 45.0     | 14                         | 42                          | 0.48           | 50          | 0201472        | 1                               |
| 50.0     | 12                         | 36                          | 0.55           | 50          | 0201474        | 1                               |
| 63.0     | 12                         | 36                          | 0.75           | 50          | 0201476        | 200                             |
| 70.0     | 12                         | 36                          | 0.84           | 50          | 0201478        | 200                             |
| 90.0     | 10                         | 30                          | 1.15           | 50          | 0201482        | 200                             |
| 102.0    | 10                         | 30                          | 1.32           | 50          | 0201484        | 200                             |
| 150.0    | 5                          | 15                          | 2.45           | 50          | 0201486        | 200                             |

Tolerance on length:  $\pm 1\%$  (ISO 1307 Standard).

Digital version



[WWW.TRELLEBORG.COM/FLUIDHANDLING](http://WWW.TRELLEBORG.COM/FLUIDHANDLING)