

# OSL



## GENERAL INDUSTRY

Water  
Suction applications



### APPLICATIONS

Suction and discharge of water, spray solutions, sand, waste water and chemical products (see chemical resistance table for PVC).

### ADVANTAGES

- Smooth bore.
- Can be supplied cut to length as required.
- Wide range of diameters.

### TECHNICAL DESCRIPTION

Inner tube: PVC, transparent, smooth.

---

Reinforcement: PVC, grey.

---

Cover: PVC, transparent, corrugated.

---

Temperature range: -10°C to +60°C.

---

### COMPLEMENTARY INFORMATION

All technical data is valid at +20°C.



**GENERAL INDUSTRY****OSL**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
25.0 ±1.0	3 -0/+0.3	31.0	6.5	16	0.8	125	0.35	25	0200960	1
30.0 ±1.0	3 -0/+0.3	36.0	6	14	0.8	135	0.4	25	0200962	1
30.0 ±1.0	3 -0/+0.3	36.0	6	14	0.8	135	0.4	50	0200963	1
40.0 ±1.0	2.5 -0/+0.3	45.0	5.5	13	0.8	160	0.54	25	0200966	1
51.0 ±1.0	3.5 -0/+0.3	58.0	5.5	13	0.8	175	0.78	25	5503088	1
75.0 ±1.0	4 -0/+0.3	83.0	3	7	0.8	188	1.27	25	0200977	1
80.0 ±1.5	4.5 -0/+0.3	89.0	3	7	0.8	240	1.45	25	0200978	1
90.0 ±1.5	5.5 -0/+0.3	101.0	3	7	0.8	270	1.85	25	0200979	1

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version



[WWW.TRELLEBORG.COM/FLUIDHANDLING](http://WWW.TRELLEBORG.COM/FLUIDHANDLING)