

# TRELLJET 561



## CONSTRUCTION & INFRASTRUCTURE

Water  
High pressure jetting



### APPLICATIONS

Specially designed for professional and industrial high pressure cleaning.

Efficient for machines, vehicles, floors, public areas, facades, etc.

Suitable for mobile pressure washers, fixed installations and reel mounted applications.

### ADVANTAGES

- ┆ Smooth cover.
- ┆ Oil, detergent, wear and weather resistant.
- ┆ High temperature resistance.
- ┆ Light weight, flexible and kink resistant.
- ┆ Long service life.

### TECHNICAL DESCRIPTION

Inner tube: NBR/SBR, black, smooth.

Reinforcement: steel, one braid.

Cover: SBR/NBR, black, smooth.

Temperature range: -40°C to +150°C.

### COUPLINGS/FITTINGS

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

### COMPLEMENTARY INFORMATION

50% of the volume in each delivery will be random lengths, shortest length of 10m, at least 50% will be in fixed length mentioned in the table.

ND 8mm



**CONSTRUCTION &  
INFRASTRUCTURE****TRELLJET 561**

ID mm	WALL THICKNESS mm	OD mm	REINF. DIAMETER mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
6.4 +0.6/-0.2	2.65	11.7 ±0.7	9.8 ±0.3	400	1000	50	0.16	100	2913930	800
7.9 +0.6/-0.2	2.75	13.4 ±0.7	11.5 ±0.3	400	1000	60	0.19	100	2910040	600
9.5 +0.6/-0.2	3	15.5 ±0.7	13.6 ±0.3	400	1000	70	0.25	100	2910000	1
12.7 +0.8/-0.4	3	18.7 ±0.8	16.7 ±0.3	350	900	80	0.3	100	5015696	1

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version



# TRELLEBORG

[WWW.TRELLEBORG.COM/FLUIDHANDLING](http://WWW.TRELLEBORG.COM/FLUIDHANDLING)