

TRELLJET 561



CONSTRUCTION & INFRASTRUCTURE

Water
High pressure jetting



APPLICATIONS

Specially designed for professional and industrial high pressure cleaning.

Efficient for machines, vehicles, floors, public areas, facades, etc.

Suitable for mobile pressure washers, fixed installations and reel mounted applications.

ADVANTAGES

- | Smooth cover.
- | Oil, detergent, wear and weather resistant.
- | High temperature resistance.
- | Light weight, flexible and kink resistant.
- | Long service life.

TECHNICAL DESCRIPTION

Inner tube: NBR/SBR, black, smooth.

Reinforcement: steel, one braid.

Cover: SBR/NBR, black, smooth.

Temperature range: -40°C to +150°C.

COUPLINGS/FITTINGS

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

COMPLEMENTARY INFORMATION

50% of the volume in each delivery will be random lengths, shortest length of 10m, at least 50% will be in fixed length mentioned in the table.

ND 8mm



**CONSTRUCTION &
INFRASTRUCTURE****TRELLJET 561**

ID mm	WALL THICKNESS mm	OD mm	REINF. DIAMETER mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
6.4 +0.6/-0.2	2.65	11.7 ±0.7	9.8 ±0.3	400	1000	50	0.16	100	2913930	
7.9 +0.6/-0.2	2.75	13.4 ±0.7	11.5 ±0.3	400	1000	60	0.19	100	2910040	
9.5 +0.6/-0.2	3	15.5 ±0.7	13.6 ±0.3	400	1000	70	0.25	100	2910000	
12.7 +0.8/-0.4	3	18.7 ±0.8	16.7 ±0.3	350	900	80	0.3	100	5015696	

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version



TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING