

# VULPANE



## GENERAL INDUSTRY

Welding hoses



### APPLICATIONS

Rubber hose for LPG (gas cylinders, heaters, welding and LPG lines).

### ADVANTAGES

- † Flexible and light weight for easy handling.
- † Long, safe service life.
- † A hose cover particularly resistant to atmospheric conditions (ozone and hot spots).
- † Special, high quality rubber compounds.
- † Very strong textile reinforcement giving high safety factor.
- † Clear branding showing gas symbol and date of manufacture.

### TECHNICAL DESCRIPTION

Inner tube: NBR/SBR, black, smooth.


Reinforcement: synthetic textile.

Cover: EPDM, orange, smooth.

Temperature range: -30 °C to +80 °C.

### STANDARD/APPROVAL

ISO 3821.



**GENERAL INDUSTRY****VULPANE**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
6.3 ±0.4	2.85	12.0 ±0.6	20	60	55	0.12	20	0200010	1
6.3 ±0.4	2.85	12.0 ±0.6	20	60	55	0.12	40	0200009	1
6.3 ±0.4	2.85	12.0 ±0.6	20	60	55	0.12	100	5501202	6600
6.3 ±0.4	2.85	12.0 ±0.6	20	60	55	0.12	120	0200008	6600
8.0 ±0.5	3	14.0 ±0.7	20	60	65	0.15	20	0200013	1
8.0 ±0.5	3	14.0 ±0.7	20	60	65	0.15	40	0200012	1
8.0 ±0.5	3	14.0 ±0.7	20	60	65	0.15	50	5012645	6650
8.0 ±0.5	3	14.0 ±0.7	20	60	65	0.15	60	5012708	6660
8.0 ±0.5	3	14.0 ±0.7	20	60	65	0.15	80	0129712	6640
8.0 ±0.5	3	14.0 ±0.7	20	60	65	0.15	100	5501203	1
8.0 ±0.5	3	14.0 ±0.7	20	60	65	0.15	120	0200011	6600
9.0 ±0.5	3.5	16.0 ±0.7	20	60	70	0.18	20	0200551	3300
9.0 ±0.5	3.5	16.0 ±0.7	20	60	70	0.18	40	0200552	1
9.0 ±0.5	3.5	16.0 ±0.7	20	60	70	0.18	120	0200553	3240
10.0 ±0.5	3.5	17.0 ±0.7	20	60	75	0.2	20	0200016	1
10.0 ±0.5	3.5	17.0 ±0.7	20	60	75	0.2	25	5010110	7000
10.0 ±0.5	3.5	17.0 ±0.7	20	60	75	0.2	40	0200015	1
10.0 ±0.5	3.5	17.0 ±0.7	20	60	75	0.2	100	5501204	7000
10.0 ±0.5	3.5	17.0 ±0.7	20	60	75	0.2	120	0200014	6960
20.0 ±0.6	3.75	27.5 ±0.8	20	60	130	0.37	40	5503077	3480

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version

**TRELLEBORG**