

VULCAIN +



GENERAL INDUSTRY

Air and water



APPLICATIONS

For pneumatic tooling or pneumatic control lines (e.g. paint spray guns).

ADVANTAGES

- † Static conductive tube.
- † Very flexible hose especially at low temperatures.
- † Suitable for hot water.

TECHNICAL DESCRIPTION

Inner tube: EPDM, black, smooth.

Reinforcement: synthetic textile.

Cover: EPDM, blue, smooth.

Temperature range: -40°C to +100°C.

Electrical properties: conductive tube, $R < 10^6 \Omega/m$.




TRELLEBORG

VULCAIN +

$R < 10^6 \Omega/m$

Made in France



**GENERAL INDUSTRY****VULCAIN +**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
6.0 ±0.4	3	12.0 ±0.5	20	80	25	0.11	20	0129662	┆
6.0 ±0.4	3	12.0 ±0.5	20	80	25	0.11	40	0129663	┆
6.0 ±0.4	3	12.0 ±0.5	20	80	25	0.11	120	0129665	┆
7.0 ±0.5	3.5	14.0 ±0.6	20	80	25	0.15	20	0129667	┆
7.0 ±0.5	3.5	14.0 ±0.6	20	80	25	0.15	40	0129668	960
7.0 ±0.5	3.5	14.0 ±0.6	20	80	25	0.15	120	0129669	960
8.0 ±0.5	3.5	15.0 ±0.6	20	60	30	0.16	20	0129670	┆
8.0 ±0.5	3.5	15.0 ±0.6	20	60	30	0.16	40	0129671	┆
8.0 ±0.5	3.5	15.0 ±0.6	20	60	30	0.16	120	0129672	┆
9.0 ±0.5	3.5	16.0 ±0.6	20	60	35	0.18	20	0129673	┆
9.0 ±0.5	3.5	16.0 ±0.6	20	60	35	0.18	40	0129675	┆
9.0 ±0.5	3.5	16.0 ±0.6	20	60	35	0.18	120	0129676	3240
10.0 ±0.5	4	18.0 ±0.6	20	60	40	0.23	20	0129678	┆
10.0 ±0.5	4	18.0 ±0.6	20	60	40	0.23	40	0129679	┆
10.0 ±0.5	4	18.0 ±0.6	20	60	40	0.23	120	0129680	┆
12.0 ±0.6	4	20.0 ±0.7	20	60	60	0.26	20	5501021	⊠
12.0 ±0.6	4	20.0 ±0.7	20	60	60	0.26	40	5501020	┆
12.0 ±0.6	4	20.0 ±0.7	20	60	60	0.26	120	5501019	2400

Tolerance on length: ±1% (ISO 1307 Standard).

⊠ Upon availability.

Digital version

**TRELLEBORG**WWW.TRELLEBORG.COM/FLUIDHANDLING