

HYDRO'ECO



AUTOMOTIVE

Oil



APPLICATIONS

Diesel, leaded and unleaded petrol, RMA (environmental friendly petrol) pressure hose in automotive applications withstanding aromatic content exceeding 50%.

Oil and grease return lines in hydraulic systems.

Also suitably in other applications for oil, grease, air and water.

ADVANTAGES

- † Special oil and petrol resistant inner tube.
- † Excellent bending radius.
- † Flexible at low and high temperatures.
- † Resistant cover to wear, oil mist, weather and ozone, abrasion.

TECHNICAL DESCRIPTION

Inner tube: NBR/PVC, black, smooth.

Reinforcement: synthetic textile.

Cover: NBR/PVC, black, smooth.

Temperature range: -30°C to +100°C.

COMPLEMENTARY INFORMATION


Available in other lengths or packaging on request.

All standard stock items delivered on white bobbins with hole ID 55mm.



TRELLEBORG

HYDRO'ECO ID x OD - WP 10 bar - year



**AUTOMOTIVE****HYDRO'ECO**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
3.0 ±0.4	2.25	7.5 ±0.5	10	30	23	0.05	20	5603911	1
4.0 ±0.4	3.5	11.0 ±0.5	10	30	30	0.11	20	0061636	1
5.0 ±0.4	3.5	12.0 ±0.5	10	30	34	0.13	20	0061637	1
6.0 ±0.4	3	12.0 ±0.5	10	30	38	0.12	20	0061638	1
7.0 ±0.5	3	13.0 ±0.6	10	30	45	0.13	20	0061639	1
8.0 ±0.5	3	14.0 ±0.6	10	30	52	0.14	20	0061640	1
10.0 ±0.5	3	17.0 ±0.6	10	30	62	0.2	10	5500140	1

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version



TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING