

OST EPDM 16BAR



GENERAL INDUSTRY

Water
Suction applications



APPLICATIONS

For suction and discharge of domestic water, industrial water, effluents, slurry and liquid manure.

ADVANTAGES

- † Wide range of diameters to suit pumps in all fields of industry.
- † Excellent flexibility.
- † Constant working pressure of 16bar throughout the range.
- † High resistance to temperatures, conductive and abrasion resistant tube.

TECHNICAL DESCRIPTION

Inner tube: EPDM, black, smooth.


Reinforcement: synthetic textile with embedded steel helix.

Cover: EPDM, black, fabric impression.

Temperature range: -40°C to +120°C.

Electrical properties: conductive tube, $R < 1M\Omega/m$.

Special properties: abrasion ISO4649: 100mm³ max.



**GENERAL INDUSTRY****OST EPDM 16BAR**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
25.0	5	35.0	16	48	0.9	100	0.68	40	5503200	∞
32.0	5	42.0	16	48	0.9	125	0.86	40	5503201	∞
38.0	5.5	49.0	16	48	0.9	150	1.03	40	5503202	∞
51.0	5.5	62.0	16	48	0.9	250	1.5	40	5503203	∞
63.0	7	77.0	16	48	0.9	325	2.31	20	59007862	∞
63.0	7	77.0	16	48	0.9	325	2.31	40	5503204	∞
76.0	7	90.0	16	48	0.9	400	2.65	20	59007863	∞
76.0	7	90.0	16	48	0.9	400	2.65	40	5503205	∞
102.0	7.5	117.0	16	48	0.9	500	3.85	20	59007864	∞
102.0	7.5	117.0	16	48	0.9	500	3.85	40	5503206	∞
127.0	9	145.0	16	48	0.9	645	6.07	20	59007865	∞
127.0	9	145.0	16	48	0.9	645	6.07	40	5513869	∞
152.0	10	172.0	16	48	0.9	910	8.53	20	59007866	∞
152.0	10	172.0	16	48	0.9	910	8.53	40	5503207	∞
203.0	13	229.0	16	48	0.9	1150	15.65	20	5503602	∞
203.0	13	229.0	16	48	0.9	1150	15.65	40	5503580	∞
254.0	15	284.0	16	48	0.9	1650	21.27	10	5503604	∞

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version

**TRELLEBORG**WWW.TRELLEBORG.COM/FLUIDHANDLING