

TRELLJET BLUE ASSEMBLY



CONSTRUCTION & INFRASTRUCTURE

Jetting, draining and spraying hoses



APPLICATIONS

For high pressure cleaning equipment (Type Kärcher).

Efficient for machines, vehicles, floors, public areas, facades, etc.

The non-staining cover is an advantage for use in food industry and public baths.

ADVANTAGES

- Non-staining smooth cover.
- Oil, detergent, wear and weather resistant.
- High working pressure.
- High temperature resistance.
- Light weight, flexible and kink resistant.
- Long service life.

TECHNICAL DESCRIPTION

Inner tube: NBR/SBR, black, smooth.

Reinforcement: 1 or 2 steel braids.

Cover: SBR/NBR, blue, smooth.

Temperature range: - 40°C to +150°C.

COUPLINGS/FITTINGS

M22F & D10 (steel).

D11 (stainless steel).

For other types of couplings, please contact us.

COMPLEMENTARY INFORMATION

Delivered in plastic bag.

Black cover can be delivered on request.



ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	TYPE	ARTICLE NUMBER	STOCK () or min. order m
7.9 +0.6 -0.2	15.0 ±0.7	650	1600	65	0.35	10	TRELLJET 580 M22F-M22F	5016813	∞
7.9 +0.6 -0.2	15.0 ±0.7	650	1600	65	0.35	20	TRELLJET 580 M22F-M22F	5016814	∞
9.5 +0.6 -0.2	17.4 ±0.7	650	1600	70	0.42	10	TRELLJET 581 M22F-M22F	5016815	∞
9.5 +0.6 -0.2	17.4 ±0.7	650	1600	70	0.42	20	TRELLJET 580 M22F-M22F	5016816	∞
9.5 +0.6 -0.2	15.5 ±0.7	400	1000	70	0.3	20	TRELLJET 581 M22F-M22F	5016812	∞

Tolerance on length: ±1% (ISO 1307 Standard).

∞ Upon availability.

Digital version



TRELLEBORG