

TEGUFLEX® P YELLOW



OIL & GAS




TECHNICAL DESCRIPTION

Inner tube Epichlorhydrin (ECO), color.

Cover Epichlorhydrin (ECO), color.

Temperature range -25 °C to 90 °C.



CE 0056 TEGUFLEX P  TRELLEBORG

TRELLEBORG IZARRA
IZARRA-ALAVA-SPAIN
Batch number - Working pressure - Testing pressure - T MAX/MIN - DN - Month/Year

**OIL & GAS****TEGUFLEX® P YELLOW**

ID mm	TYPE DE PRODUIT	WORKING PRESSURE bar	BURSTING PRESSURE bar	BL m	COMPRESSIO N mm	ELONGATION mm	LATERAL mm	ANGULAR °	WITHOUT SUPPORT RING BAR	ARTICLE NUMBER	STOCK () or min. order piece
25.0	10/16	16	50	130	30	20	20	35	0.8	5010278	1
32.0	10/16	16	50	130	30	20	20	35	0.8	0507259	1
32.0	20	16	50	130	30	20	20	35	0.8	1767430	∞
40.0	10/16	16	50	130	30	20	20	35	0.8	0507260	1
40.0	20	16	50	130	30	20	20	35	0.8	1767440	∞
50.0	10/16	16	50	130	30	20	20	35	0.7	0507258	1
50.0	20	16	50	130	30	20	20	35	0.7	1767450	∞
65.0	10/16	16	50	130	30	20	20	30	0.6	0507261	1
65.0	20	16	50	130	30	20	20	30	0.6	S1767460	∞
80.0	10/16	16	50	130	30	20	20	30	0.5	0507262	1
80.0	20	16	50	130	30	20	20	30	0.5	1767470	∞
100.0	10/16	16	50	130	30	20	20	25	0.5	0372300	1
100.0	20	16	50	130	30	20	20	25	0.5	0507764	∞
125.0	10/16	16	50	130	30	20	20	25	0.4	0507265	1
125.0	20	16	50	130	30	20	20	25	0.4	TP0125ECEC0003	∞
150.0	10/16	16	50	130	30	20	20	15	0.3	0507264	1
150.0	20	16	50	130	30	20	20	15	0.3	1796490	∞
200.0	10	16	50	130	30	20	20	15	0.3	0507399	1
200.0	16	16	50	130	30	20	20	15	0.3	0387696	1
200.0	20	16	50	130	30	20	20	15	0.3	1796500	∞
250.0	10	16	50	130	30	20	20	10	0.2	1798280	∞
250.0	16	16	50	130	30	20	20	10	0.2	0507934	∞
250.0	20	16	50	130	30	20	20	10	0.2	TP0250ECEC0004	∞
300.0	10	16	50	130	30	20	20	10	0.2	0507236	1
300.0	16	16	50	130	30	20	20	10	0.2	0508414	∞
300.0	20	16	50	130	30	20	20	10	0.2	1796520	∞

∞ Upon availability.

Digital version




TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING