

# VOLUKLER GREEN



## OIL & GAS

Oil and petroleum  
Petrol pumps



### APPLICATIONS

For equipment of petrol pumps: regular, super and unleaded petrol, biofuel, diesel fuel.

### ADVANTAGES

- † Good resistance to ageing and abrasion from repeated dragging over oily floors.
- † Complies with European standard.
- † Can be supplied with end fittings.

### TECHNICAL DESCRIPTION

Inner tube: petrol resistant NBR, black, smooth.

Reinforcement: synthetic textile, braided.


Cover: oil and weather resistant NBR/PVC, green, smooth.

Temperature range: -25 °C to +65 °C.

Electrical properties: conductive tube,  $R < 10^4 \Omega / \text{lg}$ .

### STANDARD/APPROVAL

EN 1360:2013 type 1.





OIL & GAS

VOLUKLER GREEN



ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
16.0 ±0.8	4.5	25.0 ±0.9	16	48	80	0.37	40	5513451	1920
16.0 ±0.8	4.5	25.0 ±0.9	16	48	80	0.37	80	5513452	1920

Tolerance on length: ±1% (ISO 1307 Standard).



TRELLEBORG