

# TEGUFLEX® W DW



**FOOD & BEVERAGE**



## TECHNICAL DESCRIPTION

Inner tube color.

Cover color.

Temperature range -25°C to 90°C.



TRELLEBORG IZARRA  
IZARRA-ALAVA-SPAIN  
Batch number - Working pressure - Testing pressure - T MAX/MIN - DN - Month/Year

**FOOD & BEVERAGE****TEGUFLEX® W DW**

ID mm	TYPE DE PRODUIT	WORKING PRESSURE bar	BURSTING PRESSURE bar	BL m	COMPRESSIO N mm	ELONGATION mm	LATERAL mm	ANGULAR °	WITHOUT SUPPORT RING BAR	ARTICLE NUMBER	STOCK ( ) or min. order piece
40.0	20	16	50	150	30	20	20	35	0.8	TW0040RW2RW2002	☒
50.0	20	16	50	150	30	20	20	35	0.8	TW0050RW2RW2001	☒
65.0	16	16	50	150	30	20	20	30	0.8	TW0065RW2RW2000	☒
300.0	16	10	30	200	30	20	20	10	0.3	5603097	☒
400.0	16	10	30	200	30	20	20	10	0.3	5602680	☒
600.0	16	10	30	200	30	20	20	6	0.3	5602853	☒

☒ Upon availability.

Digital version

[WWW.TRELLEBORG.COM/FLUIDHANDLING](http://WWW.TRELLEBORG.COM/FLUIDHANDLING)