

PULSOR GRAVITY



CONSTRUCTION & INFRASTRUCTURE

Concrete pump and placement



APPLICATIONS

Lay flat hose for concrete bucket (skip).

For discharge to concrete form.

ADVANTAGES

- ┆ Coil flat for easy storage and handling.
- ┆ Lightweight hose.
- ┆ Excellent resistance to wear, abrasion and weather.
- ┆ Abrasion resistance of tube <math><100\text{mm}^3</math>.

TECHNICAL DESCRIPTION

Inner tube: NR/SBR, black, smooth.

Reinforcement: synthetic textile.


Cover: NR/SBR, black, fabric impression.

Temperature range: -30°C to $+90^{\circ}\text{C}$.



TRELLEBORG

PULSOR GRAVITY



**CONSTRUCTION &
INFRASTRUCTURE****PULSOR GRAVITY**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
152.0	4.2	160.4	3	10	1.95	40	5513541	
203.0	4.5	212.0	3	10	3.8	40	5513542	
254.0	4.5	263.0	3	10	4.7	40	5513543	

Tolerance on length: $\pm 1\%$ (ISO 1307 Standard).

**TRELLEBORG**