

PROJECTOR 120



CONSTRUCTION & INFRASTRUCTURE

Spraying



APPLICATIONS

For spraying of wet mortar, mixed concrete and other wet products.

Used as a service hose between pump and nozzle in transporting plaster, grout and ready mixed concrete.

ADVANTAGES

- † High working pressure.
- † Light weight, flexible and easy to handle.
- † Abrasion resistant tube.
- † Non-staining white cover avoids traces on walls and floors.

TECHNICAL DESCRIPTION

Inner tube: wear resistant NR, black, smooth.

Reinforcement: synthetic textile.

Cover: wear and weather resistant SBR, black, fabric impression.

Temperature range: -30°C to +70°C.

Electrical properties: antistatic tube.

Special properties: abrasion resistance of tube <math><40\text{mm}^3</math> according to ISO 4649.

COMPLEMENTARY INFORMATION


13.3m lengths available on request, min. order is three pieces and by multiple of three.

Other wall thickness and/or bursting pressure on request.



TRELLEBORG

PROJECTOR 120 WP 40 BAR





ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
19.0	6	31.0	40	120	150	0.27	40	5513550	200
25.0	7	39.0	40	120	200	0.85	40	5513551	1
30.0	7	44.0	40	120	240	1	40	5513552	200
32.0	8	48.0	40	120	260	1.22	40	5513553	1
35.0	7	49.0	40	120	280	1.12	40	5513554	1
38.0	8	54.0	40	120	300	1.45	40	5513564	1
40.0	7.5	55.0	40	120	310	1.53	40	59006802	200
50.0	9	68.0	40	120	410	2.01	20	59006804	1
50.0	9	68.0	40	120	410	2.01	40	5513557	1
60.0	10	80.0	40	120	480	2.66	40	5513558	160
63.0	10	83.0	40	120	500	2.77	40	5513559	160
65.0	10	85.0	40	120	520	2.84	20	59006805	1
65.0	10	85.0	40	120	520	2.84	40	5513560	1
76.0	10	96.0	40	120	600	3.31	40	5513561	160
90.0	12	114.0	40	120	720	4.45	20	59006806	1
102.0	14	130.0	40	120	800	5.67	40	5513563	160

Tolerance on length: ±1% (ISO 1307 Standard).

☒ Upon availability.



TRELLEBORG