

OIL 10



OIL & GAS

Oil and petroleum
Discharge applications



APPLICATIONS

Mineral and synthetic oil and household fuel delivery hose (with aromatic content up to 50%).

Use not recommended for standard fuels and biofuels.

TECHNICAL DESCRIPTION


Inner tube: synthetic NBR rubber, black, smooth.

Reinforcement: synthetic textile.

Cover: synthetic NBR/SBR rubber, black, fabric impression.

Temperature range: -30 °C to +80 °C.

Electrical properties: conductive tube, $R < 10^6 \Omega/m$.



**OIL & GAS****OIL 10**

ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
16.0	26.0 ±1	10	30	130	0.43	40	5513620	
38.0	49.0 ±1	10	30	380	0.91	40	5513624	
51.0	63.0 ±1	10	30	510	1.38	40	5513625	
76.0	88.0 ±1	10	30	760	1.87	40	5513627	
102.0	115.0 ±1	10	30	1020	2.44	40	5513628	

Tolerance on length: ±1% (ISO 1307 Standard).

**TRELLEBORG**