

OIL 10 SD



OIL & GAS

Oil and petroleum

Suction and discharge applications



APPLICATIONS

Mineral and synthetic oil and household fuel suction and delivery hose (with aromatic content up to 50%).

Use not recommended for standard fuels and biofuels.

TECHNICAL DESCRIPTION


Inner tube: synthetic NBR rubber, black, smooth.

Reinforcement: synthetic textile with embedded steel helix.

Cover: synthetic NBR/SBR rubber, black, fabric impression.

Temperature range: -30°C to +80°C.

Electrical properties: conductive tube, $R < 10^6 \Omega/m$.



**OIL & GAS****OIL 10 SD**

ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
19.0	29.0 ±1	10	30	0.9	80	0.51	40	5513629	1
25.0	36.0 ±1	10	30	0.9	100	0.68	40	5513630	1
32.0	44.0 ±1	10	30	0.9	130	1.06	40	5513631	1
51.0	64.0 ±1	10	30	0.9	200	1.64	40	5513633	1
76.0	90.0 ±1	10	30	0.9	320	2.71	40	5513635	1
90.0	106.0 ±1.2	10	30	0.9	360	3.59	40	5513636	1
102.0	118.0 ±1.2	10	30	0.9	410	4.22	40	5513637	1
152.0	172.0 ±1.2	10	30	0.9	610	7.82	40	5513638	1

Tolerance on length: ±1% (ISO 1307 Standard).

**TRELLEBORG**