

AQUA 10 FG



GENERAL INDUSTRY



Kühlwasserschläuche

APPLICATIONS

Kühlwasserschlauch mit Fiberglasdecke.

TECHNICAL DESCRIPTION

Inner tube nicht leitender EPDM, color, glatt.

Reinforcement Synthetische Textileinlagen.

Cover Fiberglasgewebe, color.

Temperature range -30°C to +100°C.
+550°C Strahlungswärme.

Electrical properties $R > 10^8 \Omega/m$.





GENERAL INDUSTRY

AQUA 10 FG



ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
19.0	31.0 ±1	10	30	160	0.64	40	5503640	160
25.0	37.0 ±1	10	30	200	0.83	40	5503641	200
38.0	52.0 ±1.2	10	30	310	1.3	40	5503642	200
51.0	65.0 ±1.2	10	30	450	1.75	40	5503643	160
63.0	79.0 ±1.2	10	30	560	2.55	40	5503644	160
102.0	119.0 ±1.2	10	30	1020	3.97	40	5503639	160

Tolerance.



TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING