

ABRA 10



**CONSTRUCTION &
INFRASTRUCTURE**

Blasting and guniting



APPLICATIONS

Abrasive resistant sandblast hose used for the delivery of sand, steel shot, stone.

TECHNICAL DESCRIPTION

Inner tube: NR, black, smooth.

Reinforcement: synthetic textile.

Cover: abrasion resistant SBR, black, fabric impression.

Temperature range: -30°C to +80°C.


Electrical properties: conductive tube.

Special properties: abrasion resistance of tube <math><70\text{mm}^3</math> according to ISO 4649.



TRELLEBORG

ABRA 10





ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
13.0	27.0 ±1.2	10	30	104	0.53	40	5513716	1
16.0	30.0 ±1.2	10	30	130	0.61	40	59006824	400
19.0	33.0 ±1.2	10	30	160	0.75	40	5513717	1
25.0	39.0 ±1.2	10	30	200	0.83	40	5513718	1
32.0	48.0 ±1.2	10	30	260	1.23	40	5513719	1
38.0	56.0 ±1.2	10	30	300	1.55	40	5513720	320
51.0	71.0 ±1.2	10	30	410	2.2	40	5513721	400
63.0	83.0 ±1.2	10	30	510	2.7	40	5513722	400

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version



TRELLEBORG