

ABRA 12



**CONSTRUCTION &
INFRASTRUCTURE**

Blasting, guniting



APPLICATIONS

High abrasive resistant hose used for sandblasting (sand, steel shot, stone), spraying of mortar and mixed concrete as well as dry products (plaster, grout and ready mixed concrete).

TECHNICAL DESCRIPTION

Inner tube: wear resistant NR, black, smooth.

Reinforcement: synthetic textile.

Cover: wear and weather resistant SBR, black, fabric impression.

Temperature range: -30°C to +80°C.


Electrical properties: conductive tube.

Special properties: abrasion resistance of tube <math>< 50\text{mm}^3</math> according to ISO 4649.



TRELLEBORG

ABRA 12





ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
13.0	27.0 ±1.2	12	36	104	0.5	40	5513728	
16.0	30.0 ±1.2	12	36	130	0.61	40	5513729	
19.0	33.0 ±1.2	12	36	160	0.71	40	5513730	
25.0	39.0 ±1.2	12	36	200	0.83	40	5513731	
32.0	48.0 ±1.2	12	36	260	1.17	40	5513732	
38.0	56.0 ±1.2	12	36	300	1.8	40	5513733	
51.0	71.0 ±1.2	12	36	410	2.22	40	5513734	
63.0	85.0 ±1.6	12	36	510	2.94	40	5513735	
76.0	100.0 ±1.6	12	36	610	3.73	40	5513736	

Tolerance on length: ±1% (ISO 1307 Standard).



TRELLEBORG