

TRUCK 7 FOOD



**BULK MATERIALS
HANDLING**

Bulk tank truck discharge



APPLICATIONS

Abrasive food material delivery hose for food industry such as grain, PVC granules.

TECHNICAL DESCRIPTION

Inner tube: natural rubber, white, smooth.

Reinforcement: synthetic textile and antistatic wire.

Cover: synthetic SBR rubber, black, fabric impression.


Temperature range: -30°C to +80°C.

STANDARD/APPROVAL

EU regulations No. 1935/2004.



FDA 21 CFR 177.2600.





ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
75.0	93.0 ±1.2	7	21	2.79	40	5513671	1
90.0	102.0 ±1.2	7	21	2.14	40	5513672	1
100.0	118.0 ±1.2	7	21	3.8	40	5513673	1
102.0	122.0 ±1.2	7	21	4.32	40	5513715	1
110.0	123.0 ±1.2	7	21	2	40	5503293	1
127.0	144.0 ±1.2	7	21	4.02	40	5513674	80

Tolerance on length: ±1% (ISO 1307 Standard).

**TRELLEBORG**