

TRUCK 10 SD



**BULK MATERIALS
HANDLING**

Bulk tank truck
Suction and discharge



APPLICATIONS

Suction and delivery hose to transfer abrasive material such as cement, sand, etc.

TECHNICAL DESCRIPTION

Inner tube: natural rubber, black, smooth.

Reinforcement: synthetic textile, embedded steel helix and antistatic wire.

Cover: synthetic SBR rubber, black, fabric impression.

Temperature range: -30°C to +80°C.


Electrical properties: conductive tube.


SD



TRELLEBORG

TRUCK 10 SD





ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
76.0	98.0 ±1.6	10	30	0.9	320	4.1	40	5513675	1
90.0	108.0 ±1.6	10	30	0.9	360	4.18	40	5513676	80
102.0	126.0 ±1.6	10	30	0.9	410	5.9	40	5513677	1
127.0	153.0 ±1.6	10	30	0.9	510	8.8	40	5513678	80
152.0	178.0 ±1.6	10	30	0.9	610	10.4	40	5513679	1

Tolerance on length: ±1% (ISO 1307 Standard).



TRELLEBORG