

AQUA 10 HOT SD



GENERAL INDUSTRY

Water
Suction applications



APPLICATIONS

Hot water suction and delivery hose used in industry, construction and agricultural applications.

TECHNICAL DESCRIPTION

Inner tube: high temperature resistant EPDM, black, smooth.

Reinforcement: synthetic textile with embedded steel helix.

Cover: high temperature resistant EPDM, black, fabric impression.


Temperature range: -30°C to +100°C.

HOT SD



TRELLEBORG

AQUA 10 HOT SD



**GENERAL INDUSTRY****AQUA 10 HOT SD**

ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
38.0	48.0 ±1	10	30	0.9	160	1.01	40	5503660	1
51.0	63.0 ±1	10	30	0.9	200	1.57	40	5503661	1
63.0	75.0 ±1	10	30	0.9	245	2.21	20	59007847	1
63.0	75.0 ±1	10	30	0.9	245	2.21	40	5503662	160
76.0	88.0 ±1	10	30	0.9	320	2.43	20	59007848	1
76.0	88.0 ±1	10	30	0.9	320	2.43	40	5503663	160
102.0	116.0 ±1.2	10	30	0.9	410	3.73	20	59007849	1
102.0	116.0 ±1.2	10	30	0.9	410	3.73	40	5503654	160
127.0	143.0 ±1.2	10	30	0.9	510	5.82	20	59007850	120
127.0	143.0 ±1.2	10	30	0.9	510	5.82	40	5503655	120
152.0	169.0 ±1.2	10	30	0.9	610	8.25	20	59007851	120
152.0	169.0 ±1.2	10	30	0.9	610	8.25	40	5503656	120
203.0	225.0 ±1.2	10	30	0.8	1000	12.43	40	5503657	40
254.0	278.0 ±1.6	10	30	0.8	1270	17.39	40	5503720	40

Tolerance on length: ±1% (ISO 1307 Standard).

**TRELLEBORG**WWW.TRELLEBORG.COM/FLUIDHANDLING