

AQUA 20



AGRICULTURE



Water
Discharge applications

APPLICATIONS

Heavy duty water delivery hose, for irrigation, industrial or waste water.


TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.

Reinforcement: synthetic textile.

Cover: SBR, black, fabric impression.

Temperature range: -30°C to +80°C.



**AGRICULTURE****AQUA 20**

ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
25.0	35.0 ±1	20	60	0.71	40	5503689	200
32.0	42.0 ±1	20	60	0.95	40	5503690	200
38.0	48.0 ±1	20	60	1.08	40	5503691	200
51.0	61.0 ±1	20	60	1.22	40	5503692	200
63.0	74.0 ±1	20	60	1.71	40	5503693	1
76.0	87.0 ±1	20	60	1.9	20	59007840	1
76.0	87.0 ±1	20	60	1.9	40	5503694	160
80.0	91.0 ±1	20	60	2.09	20	59007841	∅
80.0	91.0 ±1	20	60	2.09	40	5503721	160
90.0	101.0 ±1	20	60	2.39	20	59007842	∅
90.0	101.0 ±1	20	60	2.39	40	5503722	160
102.0	114.0 ±1	20	60	2.8	20	59007843	∅
102.0	114.0 ±1	20	60	2.8	40	5503686	∅
152.0	168.0 ±1	18	54	9.13	20	59007845	1
152.0	168.0 ±1	18	54	9.13	40	5503687	120
203.0	223.0 ±1	18	54	14.7	40	5503688	40

Tolerance on length: ±1% (ISO 1307 Standard).

∅ Upon availability.

**TRELLEBORG**WWW.TRELLEBORG.COM/FLUIDHANDLING