

# AQUA 10 INDUS



## GENERAL INDUSTRY

Water  
Discharge applications



### APPLICATIONS

Heavy duty water delivery hose for tough applications in industry, agriculture and constructions sites.

### TECHNICAL DESCRIPTION

---

Inner tube: SBR, black, smooth.

---

Reinforcement: synthetic textile.


---

Cover: SBR, black, fabric impression.

---

Temperature range: -30°C to +80°C.

---





GENERAL INDUSTRY

AQUA 10 INDUS



ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
25.0	35.0 ±1	10	30	200	0.62	40	5503724	200
38.0	50.0 ±1	10	30	320	1.11	40	5503726	200
51.0	64.0 ±1.2	10	30	510	1.51	40	5503727	1
63.0	77.0 ±1.2	10	30	630	2	40	5503728	160
76.0	90.0 ±1.2	10	30	760	2.51	40	5503729	160
90.0	104.0 ±1.2	10	30	900	2.82	40	5503730	160
102.0	116.0 ±1.2	10	30	1100	3.09	40	5503731	160
127.0	142.0 ±1.2	10	30	1300	4.25	40	5503732	120
152.0	168.0 ±1.2	10	30	1600	5.43	40	5503733	120

Tolerance on length: ±1% (ISO 1307 Standard).



TRELLEBORG

[WWW.TRELLEBORG.COM/FLUIDHANDLING](http://WWW.TRELLEBORG.COM/FLUIDHANDLING)