

# MULTI 15



## GENERAL INDUSTRY

Air and water



### APPLICATIONS

Compressed air and water hose in industrial applications.

### TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.

Reinforcement: synthetic textile.

Cover: SBR, black, smooth.

Temperature range: -30°C to +70°C.

6-25mm



32-63mm





GENERAL INDUSTRY

MULTI 15



ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
6.0	12.0	15	45	30	0.13	40	5513820	3400
8.0	14.0	15	45	40	0.16	40	5513821	3400
10.0	16.0	15	45	50	0.19	40	5513822	∞
13.0	20.0	15	45	65	0.29	40	5513823	∞
16.0	23.0	15	45	80	0.34	40	5513824	1560
19.0	26.0	15	45	90	0.39	40	5513825	∞
25.0	33.0	15	45	110	0.57	40	5513826	∞
32.0	42.0	15	45	320	0.77	40	5513827	120
38.0	48.0	15	45	380	0.89	40	5513828	∞
51.0	63.0	15	45	510	1.43	40	5513829	∞
63.0	77.0	15	45	630	2	40	5513830	120

Tolerance on length: ±1% (ISO 1307 Standard).

∞ Upon availability.



TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING