

MULTI 15



GENERAL INDUSTRY

Luft und Wasser



APPLICATIONS

Pressluft- und Wasserschlauch für industrielle Anwendungen.

TECHNICAL DESCRIPTION

Inner tube SBR, color, glatt.

Reinforcement synthetische Textilgeflechte.

Cover SBR, color, glatt.

Temperature range -30°C to +70°C.

6-25mm



32-63mm





GENERAL INDUSTRY

MULTI 15



ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
6.0	12.0	15	45	30	0.13	40	5513820	
8.0	14.0	15	45	40	0.16	40	5513821	
10.0	16.0	15	45	50	0.19	40	5513822	
13.0	20.0	15	45	65	0.29	40	5513823	
16.0	23.0	15	45	80	0.34	40	5513824	
19.0	26.0	15	45	90	0.39	40	5513825	
25.0	33.0	15	45	110	0.57	40	5513826	
32.0	42.0	15	45	320	0.77	40	5513827	
38.0	48.0	15	45	380	0.89	40	5513828	
51.0	63.0	15	45	510	1.43	40	5513829	
63.0	77.0	15	45	630	2	40	5513830	

Tolerance.



TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING