

# MULTI 20



## GENERAL INDUSTRY

Air and water



### APPLICATIONS

Compressed air and water hose in industrial applications.

### TECHNICAL DESCRIPTION

Inner tube SBR, color, smooth.

Reinforcement synthetic textile.

Cover SBR, color, smooth.

Temperature range -30°C to +70°C.

6-25mm



32-102mm





GENERAL INDUSTRY

MULTI 20



ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
6.0	14.0	20	60	20	0.19	40	5513831	
8.0	16.0	20	60	30	0.23	40	5513832	
10.0	17.0	20	60	40	0.24	40	5513833	
13.0	22.0	20	60	55	0.38	40	5513834	
16.0	25.0	20	60	70	0.45	40	5513835	
19.0	29.0	20	60	80	0.58	20	5513836	
19.0	29.0	20	60	80	0.58	40	5513837	
25.0	36.0	20	60	100	0.82	40	5513838	
32.0	44.0	20	60	320	0.95	40	5513839	
38.0	52.0	20	60	380	1.2	40	5513840	
51.0	65.0	20	60	510	1.68	40	5513841	
63.0	79.0	20	60	630	2.34	40	5513842	
76.0	92.0	20	60	760	2.8	40	5513843	
102.0	120.0	20	60	1020	4.14	40	5513844	

Tolerance.



TRELLEBORG

[WWW.TRELLEBORG.COM/FLUIDHANDLING](http://WWW.TRELLEBORG.COM/FLUIDHANDLING)