

MULTI 10 OIL



GENERAL INDUSTRY



Multipurpose oil

APPLICATIONS

Versatile hose for diesel, mineral oil and grease with aromatic content <50%.

TECHNICAL DESCRIPTION

Inner tube: NBR, black, smooth.

Reinforcement: synthetic textile.

Cover: NBR, black, smooth.

Temperature range: -30°C to +100°C.

Electrical properties: conductive tube and cover, $R \leq 1M\Omega/lg$ ($R \leq 10^6 \Omega/lg$).



GENERAL INDUSTRY

MULTI 10 OIL



ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
6.0	12.0	10	40	45	0.13	40	5513845	∞
8.0	14.0	10	40	55	0.14	40	5513846	∞
10.0	17.0	10	40	60	0.21	40	5513847	∞
13.0	20.0	10	40	80	0.26	40	5513848	∞
16.0	24.0	10	40	100	0.34	40	5513849	∞
19.0	27.0	10	40	120	0.41	40	5513850	∞
25.0	34.0	10	40	150	0.6	40	5513851	∞

Tolerance on length: $\pm 1\%$ (ISO 1307 Standard).

∞ Upon availability.



TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING