

# MULTI 25 OIL



GENERAL INDUSTRY



Multipurpose oil

## APPLICATIONS

Versatile hose for diesel, mineral oil and grease with aromatic content <50%.

## TECHNICAL DESCRIPTION

---

Inner tube: NBR, black, smooth.

---

Reinforcement: synthetic textile.

---

Cover: NBR, black, smooth.

---

Temperature range: -30°C to +100°C.

---

Electrical properties: conductive tube and cover,  $R \leq 1M\Omega/lg$  ( $R \leq 10^6 \Omega/lg$ ).

---



GENERAL INDUSTRY

MULTI 25 OIL



ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
6.0	13.0	25	80	40	0.14	40	5513852	
8.0	15.0	25	80	50	0.17	40	5513853	
10.0	17.0	25	80	60	0.19	40	5513854	
13.0	21.0	25	80	80	0.28	40	5513855	
16.0	25.0	25	80	100	0.33	40	5513856	
19.0	28.0	25	80	120	0.43	40	5513857	
25.0	35.0	25	80	150	0.61	40	5513858	

Tolerance on length:  $\pm 1\%$  (ISO 1307 Standard).



TRELLEBORG

[WWW.TRELLEBORG.COM/FLUIDHANDLING](http://WWW.TRELLEBORG.COM/FLUIDHANDLING)