

PROJECTOR 40



CONSTRUCTION & INFRASTRUCTURE

Spraying



APPLICATIONS

For spraying of mortar and mixed concrete as well as dry products.

Used as a service hose between pump and nozzle in transporting plaster, grout and ready mixed concrete.

ADVANTAGES

- ¹ Light weight, flexible and is easy to handle.
- ¹ Abrasion resistant tube compound.
- ¹ Conductive inner tube compound gives increased safety for the operator.

TECHNICAL DESCRIPTION

Inner tube: wear resistant NR, black, smooth.

Reinforcement: synthetic textile.

Cover: wear and weather resistant SBR, black, fabric impression.

Temperature range: -30°C to +70°C.


Electrical properties: conductive tube, $R < 2 \cdot 10^6 \Omega/m$.

Special properties: abrasion resistance of tube $< 40mm^3$ according to ISO 4649.



TRELLEBORG

PROJECTOR 40 WP 12 BAR



CONSTRUCTION & INFRASTRUCTURE			PROJECTOR 40						
ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (.) or min. order m
25.0	9.5 ±0.50	44.0 ±1.0	12	40	120	1.2	40	59006811	120
32.0	10 ±0.50	52.0 ±1.0	12	40	150	1.57	40	59006812	1
40.0	10 ±0.50	60.0 ±1.0	12	40	180	1.8	20	59006813	1
40.0	10 ±0.50	60.0 ±1.0	12	40	180	1.8	40	59006814	1
50.0	10 ±0.75	70.0 ±1.5	12	40	250	2.22	20	59006815	1
50.0	10 ±0.75	70.0 ±1.5	12	40	250	2.22	40	59006816	1
60.0	10 ±0.75	80.0 ±1.5	12	40	290	2.3	20	59006817	480
60.0	10 ±0.75	80.0 ±1.5	12	40	290	2.3	40	59006818	1
63.0	13.5 ±0.75	90.0 ±1.5	12	40	340	2.83	20	59006949	☒
65.0	10 ±0.75	85.0 ±1.5	12	40	320	2.7	20	59006819	1
65.0	10 ±0.75	85.0 ±1.5	12	40	320	2.7	40	59006820	1
Tolerance on length: ±1% (ISO 1307 Standard).									☒ Upon availability.

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING