

RED WATER



GENERAL INDUSTRY

Air and water



APPLICATIONS

Water discharge under pressure on industrial or urban sites.

ADVANTAGES

- ¹ Sturdy hose.
- ¹ Good resistance to abrasion thanks to wall thickness.

TECHNICAL DESCRIPTION

Inner tube: SBR for ID≤25mm, EPDM for ID>25mm, black, smooth.


Reinforcement: synthetic textile.

Cover: SBR, red, smooth for ID≤25mm, fabric impression for ID>25mm.

Temperature range: -25 °C to +70 °C.

TRELLEBORG

RED WATER



**GENERAL INDUSTRY****RED WATER**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (.) or min. order m
13.0	4	21.0	10	30	78	0.36	40	5503031	1
16.0	4	24.0	10	30	96	0.43	20	5503404	1
16.0	4	24.0	10	30	96	0.43	40	5503040	1
19.0	4.5	28.0	10	30	115	0.56	20	5503405	1
19.0	4.5	28.0	10	30	115	0.56	40	5503032	1
25.0	5	35.0	10	30	150	0.8	20	5503406	1
25.0	5	35.0	10	30	150	0.8	40	5503033	1
32.0	5.5	43.0	10	30	200	0.9	40	5503034	1
38.0	6	50.0	10	30	210	1	40	5503035	1
50.0	7	65.0	10	30	400	1.6	40	5503036	1

Tolerance on length: $\pm 1\%$ (ISO 1307 Standard).

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING