

# CASCADE



## GENERAL INDUSTRY

Air and water



### APPLICATIONS

Water discharge under pressure on industrial or urban sites and all water discharge applications in building and public works.

### ADVANTAGES

- <sup>1</sup> Extremely resistant to ageing and atmospheric conditions.
- <sup>1</sup> Highly flexible and easy-to-hold due to the fluted cover.

### TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.


Reinforcement: synthetic textile.

Cover: EPDM, green, fluted.

Temperature range: -30°C to +70°C.

### STANDARD/APPROVAL

In compliance with ISO 1403 type 2 (except branding).



**GENERAL INDUSTRY****CASCADE**

| ID<br>mm  | WALL<br>THICKNESS<br>mm | OD<br>mm  | WORKING<br>PRESSURE<br>bar | BURSTING<br>PRESSURE<br>bar | BENDING<br>RADIUS<br>mm | WEIGHT<br>kg/m | LENGTH<br>m | ARTICLE<br>NUMBER | STOCK (.) or<br>min. order<br>m |
|-----------|-------------------------|-----------|----------------------------|-----------------------------|-------------------------|----------------|-------------|-------------------|---------------------------------|
| 12.7 ±0.6 | 4                       | 20.7 ±0.7 | 10                         | 30                          | 70                      | 0.28           | 40          | 0061510           | 1520                            |
| 15.8 ±0.7 | 4.1                     | 24.0 ±0.8 | 10                         | 30                          | 80                      | 0.34           | 20          | 0061521           | 1                               |
| 15.8 ±0.7 | 4.1                     | 24.0 ±0.8 | 10                         | 30                          | 80                      | 0.34           | 40          | 0061520           | 1                               |
| 15.8 ±0.7 | 4.1                     | 24.0 ±0.8 | 10                         | 30                          | 80                      | 0.34           | 80          | 0061522           | 1360                            |
| 19.4 ±0.7 | 4.5                     | 28.4 ±0.8 | 10                         | 30                          | 120                     | 0.45           | 20          | 0061541           | 1                               |
| 19.4 ±0.7 | 4.5                     | 28.4 ±0.8 | 10                         | 30                          | 120                     | 0.45           | 40          | 0061540           | 1                               |
| 19.4 ±0.7 | 4.5                     | 28.4 ±0.8 | 10                         | 30                          | 120                     | 0.45           | 80          | 0061542           | 1                               |
| 25.4 ±1.0 | 4.8                     | 35.0 ±1.1 | 10                         | 30                          | 150                     | 0.6            | 20          | 0061551           | 1                               |
| 25.4 ±1.0 | 4.8                     | 35.0 ±1.1 | 10                         | 30                          | 150                     | 0.6            | 40          | 0061550           | 1                               |

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version

