

TRELLJET 560



CONSTRUCTION & INFRASTRUCTURE

Water
High pressure jetting



APPLICATIONS

Specially designed for professional and industrial high pressure cleaning.

Efficient for machines, vehicles, floors, public areas, facades, etc.

Suitable for mobile pressure washers, fixed installations and reel mounted applications.

ADVANTAGES

- | Smooth cover.
- | Oil, detergent, wear and weather resistant.
- | High working pressure.
- | High temperature resistance.
- | Light weight, flexible and kink resistant.
- | Long service life.

TECHNICAL DESCRIPTION

Inner tube: NBR/SBR, black, smooth.

Reinforcement: steel, two braids.

Cover: SBR/NBR, black, smooth.

Temperature range: -40°C to +150°C.


COUPLINGS/FITTINGS

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

COMPLEMENTARY INFORMATION



50% of the volume in each delivery will be random lengths, shortest length of 10m, at least 50% will be in fixed length mentioned in the table.

ND 8mm



TRELLEBORG

TRELLJET 560 - ND 08 - 5/16" - WP 650 BAR/9560 PSI - MAX 150 °C - 1 Q 13 - Made in France

 CONSTRUCTION & INFRASTRUCTURE			TRELLJET 560							
ID mm	WALL THICKNESS mm	OD mm	REINF. DIAMETER mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
7.9 +0.6/-0.2	3.55	15.0 ±0.7	12.7 ±0.3	650	1600	65	0.31	100	2910220	700
9.5 +0.6/-0.2	3.8	17.4 ±0.7	14.9 ±0.3	650	1600	70	0.38	100	2910260	1
Tolerance on length: ±1% (ISO 1307 Standard).										

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING