TRELLJET 581

CONSTRUCTION & INFRASTRUCTURE

Water
High pressure jetting

APPLICATIONS

Specially designed for professional and industrial high pressure cleaning.

Efficient for machines, vehicles, floors, public areas, facades, etc.

The non-staining cover is also an advantage for use in food industry and public baths.

Suitable for mobile pressure washers, fixed installations and reel mounted applications.

ADVANTAGES

- Non-staining smooth cover.
- Oil, detergent, wear and weather resistant.
- High temperature resistance.
- Light weight, flexible and kink resistant.
- Long service life.

TECHNICAL DESCRIPTION

Inner tube: NBR/SBR, black, smooth.
Reinforcement: steel, one braid.
Cover: SBR/NBR, blue, smooth.
Temperature range: -40°C to +150°C.

COUPLINGS/FITTINGS

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

COMPLEMENTARY INFORMATION

50% of the volume in each delivery will be random lengths, shortest length of 10m, at least 50% will be in fixed length mentioned in the table.



CONSTRUCTION & INFRASTRUCTURE

TRELLJET 581



ID mm	WALL THICKNESS mm	OD mm	REINF. DIAMETER mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (l) or min. order m
6.4 +0.6/-0.2	2.65	11.7 ±0.7	9.8 ±0.3	400	1000	50	0.16	100	2910430	l
9.5 +0.6/-0.2	3	15.5 ±0.7	13.6 ±0.3	400	1000	70	0.25	100	2910450	l
12.7 +0.8/-0.4	3	18.7 ±0.8	16.7 ±0.3	350	900	80	0.3	100	2910470	l

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version

TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING