

VULCAIN +



GENERAL INDUSTRY

Air and water



APPLICATIONS

For pneumatic tooling or pneumatic control lines (e.g. paint spray guns).

ADVANTAGES

- ¹ Static conductive tube.
- ¹ Very flexible hose especially at low temperatures.
- ¹ Suitable for hot water.

TECHNICAL DESCRIPTION

Inner tube: EPDM, black, smooth.

Reinforcement: synthetic textile.

Cover: EPDM, blue, smooth.

Temperature range: -40°C to +100°C.

Electrical properties: conductive tube, $R < 10^6 \Omega/m$.



GENERAL INDUSTRY

VULCAIN +



ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (.) or min. order m
6.0 ±0.4	3	12.0 ±0.5	20	80	25	0.11	20	0129662	1
6.0 ±0.4	3	12.0 ±0.5	20	80	25	0.11	40	0129663	1
6.0 ±0.4	3	12.0 ±0.5	20	80	25	0.11	120	0129665	1
7.0 ±0.5	3.5	14.0 ±0.6	20	80	25	0.15	20	0129667	1
7.0 ±0.5	3.5	14.0 ±0.6	20	80	25	0.15	40	0129668	960
7.0 ±0.5	3.5	14.0 ±0.6	20	80	25	0.15	120	0129669	960
8.0 ±0.5	3.5	15.0 ±0.6	20	60	30	0.16	20	0129670	1
8.0 ±0.5	3.5	15.0 ±0.6	20	60	30	0.16	40	0129671	1
8.0 ±0.5	3.5	15.0 ±0.6	20	60	30	0.16	120	0129672	1
9.0 ±0.5	3.5	16.0 ±0.6	20	60	35	0.18	20	0129673	1
9.0 ±0.5	3.5	16.0 ±0.6	20	60	35	0.18	40	0129675	1
9.0 ±0.5	3.5	16.0 ±0.6	20	60	35	0.18	120	0129676	3240
10.0 ±0.5	4	18.0 ±0.6	20	60	40	0.23	20	0129678	1
10.0 ±0.5	4	18.0 ±0.6	20	60	40	0.23	40	0129679	1
10.0 ±0.5	4	18.0 ±0.6	20	60	40	0.23	120	0129680	1
12.0 ±0.6	4	20.0 ±0.7	20	60	60	0.26	20	5501021	☒
12.0 ±0.6	4	20.0 ±0.7	20	60	60	0.26	40	5501020	1
12.0 ±0.6	4	20.0 ±0.7	20	60	60	0.26	120	5501019	2400

Tolerance on length: ±1% (ISO 1307 Standard).

☒ Upon availability.

Digital version


TRELLEBORGWWW.TRELLEBORG.COM/FLUIDHANDLING