

# HYDRO'ECO



## AUTOMOTIVE

Oil



### APPLICATIONS

Diesel, leaded and unleaded petrol, RMA (environmental friendly petrol) pressure hose in automotive applications withstanding aromatic content exceeding 50%.

Oil and grease return lines in hydraulic systems.

Also suitably in other applications for oil, grease, air and water.

### ADVANTAGES

- ▮ Special oil and petrol resistant inner tube.
- ▮ Excellent bending radius.
- ▮ Flexible at low and high temperatures.
- ▮ Resistant cover to wear, oil mist, weather and ozone, abrasion.

### TECHNICAL DESCRIPTION

Inner tube: NBR/PVC, black, smooth.

Reinforcement: synthetic textile.

Cover: NBR/PVC, black, smooth.



Temperature range: -30 °C to +100 °C.

### COMPLEMENTARY INFORMATION

Available in other lengths or packaging on request.

All standard stock items delivered on white bobbins with hole ID 55mm.



 <b>AUTOMOTIVE</b>			<b>HYDRO'ECO</b>						
ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
4.0 ±0.4	3.5	11.0 ±0.5	10	30	30	0.11	20	0061636	1
5.0 ±0.4	3.5	12.0 ±0.5	10	30	34	0.13	20	0061637	1
6.0 ±0.4	3	12.0 ±0.5	10	30	38	0.12	20	0061638	1
7.0 ±0.5	3	13.0 ±0.6	10	30	45	0.13	20	0061639	1
8.0 ±0.5	3	14.0 ±0.6	10	30	52	0.14	20	0061640	1
10.0 ±0.5	3	17.0 ±0.6	10	30	62	0.2	10	5500140	1
Tolerance on length: ±1% (ISO 1307 Standard).									

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING