

SOLVYKLER



GENERAL INDUSTRY

Hot water and multipurpose
chemicals



APPLICATIONS

Pressure service line for ester, ketone, alcohol based paints and numerous chemicals.

ADVANTAGES

- ¹ Hose cover resistant to splashing of corrosive chemicals.
- ¹ Free from silicone.
- ¹ Hose remains flexible within a wide temperature range.
- ¹ Antistatic tube.

TECHNICAL DESCRIPTION

Inner tube: chemical resistant EPDM, black, smooth.

Reinforcement: synthetic textile.

Cover: chemical and weather resistant EPDM, green, smooth.

Temperature range: -30°C to +100°C.

Electrical properties: antistatic tube, $R < 10^6 \Omega/m$.

COUPLINGS/FITTINGS

Special paint hose couplings are recommended.



GENERAL INDUSTRY

SOLVYKLER



ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (.) or min. order m
6.0 ±0.4	3.3	12.6 ±0.5	20	60	60	0.13	20	0060304	☒
6.0 ±0.4	3.3	12.6 ±0.5	20	60	60	0.13	40	0060305	1
6.0 ±0.4	3.3	12.6 ±0.5	20	60	60	0.13	80	0060306	1520
6.0 ±0.4	3.3	12.6 ±0.5	20	60	60	0.13	120	0060307	3240
8.0 ±0.5	3.5	15.0 ±0.6	20	60	70	0.16	40	0060309	1
8.0 ±0.5	3.5	15.0 ±0.6	20	60	70	0.16	80	0060310	1120
8.0 ±0.5	3.5	15.0 ±0.6	20	60	70	0.16	120	0060311	1080
9.0 ±0.5	3.5	16.0 ±0.6	20	60	85	0.17	20	0060281	☒
9.0 ±0.5	3.5	16.0 ±0.6	20	60	85	0.17	40	0060282	1
9.0 ±0.5	3.5	16.0 ±0.6	20	60	85	0.17	80	0060283	1120
9.0 ±0.5	3.5	16.0 ±0.6	20	60	85	0.17	120	0060285	1080
10.0 ±0.5	4	18.0 ±0.6	20	60	90	0.22	40	0060313	1
10.0 ±0.5	4	18.0 ±0.6	20	60	90	0.22	80	0060314	3280
10.0 ±0.5	4	18.0 ±0.6	20	60	90	0.22	120	0060315	3240
13.0 ±0.6	4	21.0 ±0.7	20	60	110	0.27	20	0060718	☒
13.0 ±0.6	4	21.0 ±0.7	20	60	110	0.27	40	0060719	1
13.0 ±0.6	4	21.0 ±0.7	20	60	110	0.27	80	0060720	☒
13.0 ±0.6	4	21.0 ±0.7	20	60	110	0.27	120	0060721	1
16.0 ±0.8	4	24.0 ±1.0	20	60	130	0.32	20	0070139	1140
16.0 ±0.8	4	24.0 ±1.0	20	60	130	0.32	40	0070140	☒
16.0 ±0.8	4	24.0 ±1.0	20	60	130	0.32	80	0070141	☒
20.0 ±0.8	4.5	29.0 ±1.0	20	60	150	0.44	20	0070142	☒
20.0 ±0.8	4.5	29.0 ±1.0	20	60	150	0.44	40	0070143	1
20.0 ±0.8	4.5	29.0 ±1.0	20	60	150	0.44	80	0070144	1
25.0 ±1.2	4.5	34.0 ±1.5	20	60	170	0.54	20	0070145	☒
25.0 ±1.2	4.5	34.0 ±1.5	20	60	170	0.54	40	0070146	1
25.0 ±1.2	4.5	34.0 ±1.5	20	60	170	0.54	80	0070147	☒

Tolerance on length: ±1% (ISO 1307 Standard).

☒ Upon availability.

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING