

MULTIKLER



GENERAL INDUSTRY

Multipurpose oil



APPLICATIONS

Pressure service line for benzene, toluene and xylene based paints, lacquer, varnish and certain chemicals.

Also for industrial paint spray equipment.

ADVANTAGES

- ¹ Hose cover resistant both to abrasion and to corrosive chemicals.
- ¹ Free from silicone.
- ¹ Antistatic tube.

TECHNICAL DESCRIPTION

Inner tube: solvent paints resistant NBR, black, smooth.

Reinforcement: synthetic textile.


Cover: oil and weather resistant NBR/PVC, green, smooth.

Temperature range: -20°C to +100°C.

Electrical properties: antistatic tube, $R < 10^6 \Omega/m$.

COUPLINGS/FITTINGS

Special paint hose couplings are recommended.





GENERAL INDUSTRY

MULTIKLER



ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (.) or min. order m
6.0 ±0.4	3.3	12.6 ±0.5	20	60	60	0.14	40	0064197	☒
6.0 ±0.4	3.3	12.6 ±0.5	20	60	60	0.14	80	0064198	☒
6.0 ±0.4	3.3	12.6 ±0.5	20	60	60	0.14	120	0064199	☒
8.0 ±0.5	3.5	15.0 ±0.6	20	60	70	0.17	20	0064201	☒
8.0 ±0.5	3.5	15.0 ±0.6	20	60	70	0.17	40	0064202	1
8.0 ±0.5	3.5	15.0 ±0.6	20	60	70	0.17	80	0064203	☒
8.0 ±0.5	3.5	15.0 ±0.6	20	60	70	0.17	120	0064204	1
10.0 ±0.5	3.75	17.5 ±0.6	20	60	90	0.24	20	0064207	1
10.0 ±0.5	3.75	17.5 ±0.6	20	60	90	0.24	40	0064208	1
10.0 ±0.5	3.75	17.5 ±0.6	20	60	90	0.24	80	0064209	☒
10.0 ±0.5	3.75	17.5 ±0.6	20	60	90	0.24	120	0064210	☒
13.0 ±0.6	4	21.0 ±0.7	20	60	110	0.28	20	0064211	☒
13.0 ±0.6	4	21.0 ±0.7	20	60	110	0.28	40	0064212	1
13.0 ±0.6	4	21.0 ±0.7	20	60	110	0.28	80	0064213	☒
13.0 ±0.6	4	21.0 ±0.7	20	60	110	0.28	120	0064214	☒
16.0 ±0.7	4.5	25.0 ±0.8	20	60	130	0.38	40	0064216	800
16.0 ±0.7	4.5	25.0 ±0.8	20	60	130	0.38	80	0064217	☒
16.0 ±0.7	4.5	25.0 ±0.8	20	60	130	0.38	120	0064218	☒

Tolerance on length: ±1% (ISO 1307 Standard).

☒ Upon availability.

Digital version


TRELLEBORGWWW.TRELLEBORG.COM/FLUIDHANDLING