

FP 3010



AQUACULTURE

Farm
Pumping fish



APPLICATIONS

Used for pumping fish in fish farms and fish processing factories.

ADVANTAGES

- ¹ Flexible hose design providing optimum characteristics for this application.
- ¹ Withstands rough handling.
- ¹ Without helix for discharge applications.

TECHNICAL DESCRIPTION

Inner tube: wear resistant SBR/NBR, black, smooth.

Reinforcement: synthetic textile.

Cover: weather resistant SBR/NBR, black, fabric impression.

Temperature range: -40°C to +80°C.

COMPLEMENTARY INFORMATION

Other lengths available on request.



and in opposite:



 AQUACULTURE			FP 3010					
ID inch	ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (1) or min. order m
10	254.0	263.0 ±1.5	3	10	4.06	40	2955660	40
10	254.0	265.0 ±1.5	3	10	5.12	40	2863290	40
12	305.0	312.0 ±1.5	3	10	3.83	40	2861070	40
12	305.0	314.0 ±1.5	3	10	5.03	40	2913530	40
12	305.0	316.0 ±1.5	3	10	6.3	40	2911310	40
14	355.0	362.0 ±1.5	3	10	4.44	40	2860840	40
14	355.0	364.0 ±1.5	3	10	5.84	20	1300190	40
14	355.0	364.0 ±1.5	3	10	5.84	40	2052650	40
14	355.0	366.0 ±1.5	3	10	7.3	40	5500653	40
Tolerance on length: ±1% (ISO 1307 Standard).								

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING