

PUSH-LOCK RED



GENERAL INDUSTRY

Auto process



APPLICATIONS

Ideally designed for hydraulic pneumatic low pressure lines for robotic in automotive industries.

Used with push-on fittings at maximum working pressure of 16bar (250psi).

Not suitable for impulse pressure application.

ADVANTAGES

- ¹ 40, 80 and 100m delivered in one piece on wooden reel.
- ¹ Very good abrasion resistance.
- ¹ Flexibility, light weight and easy handling.
- ¹ Free from silicone.

TECHNICAL DESCRIPTION

Inner tube: oil resistant NBR/PVC, black, smooth.

Reinforcement: one textile braid.

Cover: abrasion, oil and weather resistant NBR/PVC, red, smooth.

Temperature range:

Air: -20 °C/+110 °C (peak +125 °C).

Water: 0 °C/+100 °C (peak +110 °C).

Hydraulic oils: -20 °C/+70 °C (peak +90 °C).

Water glycol: -20 °C/+ 70 °C (peak +90 °C).

Electrical properties: non-conductive inner tube, $R > 10^{12} \Omega/m$.

COUPLINGS/FITTINGS

Used with push-on fittings at maximum working pressure of 16bar (250psi).

COMPLEMENTARY INFORMATION

40, 80 and 100m: delivered in one piece on wooden reel.

20m: delivered in coils with PE film on pallet.



TRELLEBORG



PUSH-LOCK HOSE ND WP 16 BAR XQY



**GENERAL INDUSTRY****PUSH-LOCK RED**

ID inch	ID mm	OD mm	WORKING PRESSURE bar psi	BURSTING PRESSURE bar psi	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (.) or min. order m
1/4	6.3 ±0.4	12.4 ±0.8	16 250.0	64 1000.0	45	0.12	20	5503516	∞
1/4	6.3 ±0.4	12.4 ±0.8	16 250.0	64 1000.0	45	0.12	40	5503517	∞
1/4	6.3 ±0.4	12.4 ±0.8	16 250.0	64 1000.0	45	0.12	100	5503518	1
3/8	9.6 ±0.5	15.5 ±0.8	16 250.0	64 1000.0	75	0.16	20	5503519	∞
3/8	9.6 ±0.5	15.5 ±0.8	16 250.0	64 1000.0	75	0.16	40	5503520	∞
3/8	9.6 ±0.5	15.5 ±0.8	16 250.0	64 1000.0	75	0.16	100	5503521	1
1/2	12.7 ±0.6	18.7 ±1.0	16 250.0	64 1000.0	90	0.19	20	5503522	∞
1/2	12.7 ±0.6	18.7 ±1.0	16 250.0	64 1000.0	90	0.19	40	5503523	1
1/2	12.7 ±0.6	18.7 ±1.0	16 250.0	64 1000.0	90	0.19	100	5503524	1
5/8	16.0 ±0.6	22.9 ±1.0	16 250.0	64 1000.0	115	0.28	20	5503525	∞
5/8	16.0 ±0.6	22.9 ±1.0	16 250.0	64 1000.0	115	0.28	40	5503526	1
5/8	16.0 ±0.6	22.9 ±1.0	16 250.0	64 1000.0	115	0.28	80	5503527	1
3/4	19.2 ±0.6	26.5 ±1.0	16 250.0	64 1000.0	135	0.34	20	5503528	∞
3/4	19.2 ±0.6	26.5 ±1.0	16 250.0	64 1000.0	135	0.34	40	5503529	∞
3/4	19.2 ±0.6	26.5 ±1.0	16 250.0	64 1000.0	135	0.34	80	5503530	1

Tolerance on length: ±1% (ISO 1307 Standard).

∞ Upon availability.

Digital version


TRELLEBORGWWW.TRELLEBORG.COM/FLUIDHANDLING